

FREE-STAND TYPE 4



These enclosures are ideal for mounting equipment on panels or racks in indoor or outdoor applications where it is necessary to protect controls and instrumentation from wet, non-corrosive environments.

FEATURES & BENEFITS

- Seams continuously welded and ground smooth; no holes or knockouts
- Internal mounting channels welded horizontally at top, bottom and center
- Panels and rack-mounting angles can be mounted anywhere along channels
- Return flange around three sides of door and along enclosure opening excludes liquids and contaminants
- Stainless steel door clamps assure water-tight seal
- Hasp and staple provided for padlocking
- Data pocket is high-impact thermoplastic
- Lifting eyes for easy handling
- Oil-resistant door gasket
- Bonding provision on door
- Provision for mounting fluorescent light

SPECIFICATIONS

- Color** Gray
- Color Code** ANSI 61
- Finish** Powder Coated
- Thickness** 2.66 mm

Table 1/1

Catalog Number	Height	Width	Depth	Protection Rating	Material	Rack Unit Quantity

A72H2518FS	1830 mm	637 mm	459 mm	NEMA Type 4; NEMA Type 3; NEMA Type 12; NEMA Type 13; IP66	Mild Steel	35
A72H3124FS	1830 mm	789 mm	611 mm	NEMA Type 4; NEMA Type 3; NEMA Type 12; NEMA Type 13; IP66	Mild Steel	35
A72H3724FS	1830 mm	941 mm	611 mm	NEMA Type 4; NEMA Type 3; NEMA Type 12; NEMA Type 13; IP66	Mild Steel	35

Order panels separately.

2100 Hoffman Way
Anoka, MN 55303-1745 | USA
763.421.2240



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2023 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.