

# QUIET VORTEX A/C ENCLOSURE COOLERS TYPE 4/4X/12

Vortex A/C Enclosure Coolers keep enclosures cool, clean and protected even in the harshest environments. Offering flexible installation, these enclosure coolers are ideal in space-restrictive areas where compressed air is readily available. With almost no moving parts, these enclosure coolers are highly reliable and virtually maintenance free.



## FEATURES & BENEFITS

Quieter operation with noise level of 60-75 dB

Top, side, and front mount allows for versatile installation in confined areas

Operates in environments up to 175 F (80 C)

Cooling capacities up to 5000 BTU/Hr. (1465 W)

Mechanical thermostat reduces energy consumption

NEMA Type 4,4X models are polycarbonate and stainless steel exterior; aluminum and brass internal components

NEMA Type 12 models are polycarbonate and aluminum exterior; aluminum and brass internal components

Supplied with five-micron, automatic drain compressed air filter, cold ducting kit, and cold air muffler

## SPECIFICATIONS

**Color** Light Gray

**Color Code** RAL 7035

**Finish** Smooth Matte

Table 1/2

Catalog Number	Height	Width	Depth	Nominal Capacity Btu/h	Nominal Capacity Watts	Protection Rating
----------------	--------	-------	-------	------------------------	------------------------	-------------------

VA1516012	203 mm	121 mm	137 mm	1500 Btu/h	440 W	NEMA Type 12; NEMA Type 4; NEMA Type 4X
VA2516012	203 mm	121 mm	137 mm	2500 Btu/h	733 W	NEMA Type 12; NEMA Type 4; NEMA Type 4X
VA5016012	164 mm	240 mm	141 mm	5000 Btu/h	1465 W	NEMA Type 12; NEMA Type 4; NEMA Type 4X
VA0916012	203 mm	121 mm	137 mm	900 Btu/h	264 W	NEMA Type 12; NEMA Type 4; NEMA Type 4X
VA151604X	203 mm	121 mm	137 mm	1500 Btu/h	440 W	NEMA Type 12; NEMA Type 4; NEMA Type 4X
VA251604X	203 mm	121 mm	137 mm	2500 Btu/h	733 W	NEMA Type 12; NEMA Type 4; NEMA Type 4X
VA501604X	164 mm	240 mm	141 mm	5000 Btu/h	1465 W	NEMA Type 12; NEMA Type 4; NEMA Type 4X
VA091604X	203 mm	121 mm	137 mm	900 Btu/h	264 W	NEMA Type 12; NEMA Type 4; NEMA Type 4X

Table 2/2

Catalog Number	Material
VA1516012	Polycarbonate
VA2516012	Polycarbonate
VA5016012	Polycarbonate
VA0916012	Polycarbonate
VA151604X	Polycarbonate
VA251604X	Polycarbonate
VA501604X	Polycarbonate
VA091604X	Polycarbonate

2100 Hoffman Way  
Anoka, MN 55303-1745 | USA  
763.421.2240



Our powerful portfolio of brands:  
[nVent.com](https://www.nvent.com) **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.  
nVent reserves the right to change specifications without notice.