














**HOFFMAN**

**PROLINE™**



|   |  |  |
|---|--|--|
| <p>1</p>  <p>(1X)</p>              | <p>2</p>  <p>(1X)</p>  | <p>3</p>  <p>(1X)</p>           |
| <p>4</p> <p>M5x10</p>  <p>(2X)</p> | <p>5</p>  <p>(6X)</p> | <p>6</p> <p>M5</p>  <p>(4X)</p> |
| <p>7</p>  <p>(4X)</p>              |  |  |







**HOFFMAN**